




C(D)Q2W, Compact Cylinder, Double Acting Double Rod w/Auto Switch Mounting Groove CDQ2WA50-50DZ

- Double acting, double rod, compact cylinder
- Bore sizes (mm): 12, 16, 20, 25, 32, 40, 50, 63, 80, 100
- Standard stroke range (mm): 5 to 100
- Port threads: M (12 to 25 bore); Rc, NPT or G (32 to 100 bore)
- Can mount small auto switches on 4 surfaces.

Magnet	D (Built-in)
Mounting	A (Both Ends Tapped)
Type	Standard
Bore Size	Ø50 mm
Port Thread Type	Rc
Stroke	50
Body Option	Standard (Rod End Female Thread)
Auto Switch Groove	None, also for 12-25 Bore w/o Magnet
Auto Switch	No Switch
Lead Wire or Prewired Connector	Z (5 m)
Number	2 pcs. or None in the Case of No Switch
Rod End Options	None
Temperature Resistance	None
Low Speed	None
Made of Stainless Steel	None
Fluororubber Seal	None
-	Compressed air
Weight	0.897 Kg



p.32 ~ c50

カーボンイオン銃

カーボンイオン銃は、炭素の蒸気源を加熱して発生させた炭素イオンを、高電圧で加速して、試料表面に照射する装置です。

※本カタログに掲載の製品は、すべて標準仕様です。オプション仕様は、別途要料となります。

C-50



C-50は、高電圧で加速された炭素イオンを、試料表面に照射する装置です。主に、表面分析や、表面改質に利用されます。

C-100



C-100は、高電圧で加速された炭素イオンを、試料表面に照射する装置です。主に、表面分析や、表面改質に利用されます。

C-200



C-200は、高電圧で加速された炭素イオンを、試料表面に照射する装置です。主に、表面分析や、表面改質に利用されます。

C-300



C-300は、高電圧で加速された炭素イオンを、試料表面に照射する装置です。主に、表面分析や、表面改質に利用されます。

C-400



C-400は、高電圧で加速された炭素イオンを、試料表面に照射する装置です。主に、表面分析や、表面改質に利用されます。

C-500



C-500は、高電圧で加速された炭素イオンを、試料表面に照射する装置です。主に、表面分析や、表面改質に利用されます。

-

-

CQ2-Z-B_EU.pdf